



TECNOSERVICE'21 srl

by Tinti Sergio
Via Carlo Pisacane, 134
61032 Fano (PU) Italy
P.IVA IT0200411413

Tel. +39 0721 805911
FAX +39 0721 809794
e-mail: staff@technochef.it
www.technochef.it
www.technochef.eu

Services and Technologies for professional catering since 1973



CODE	DESCRIPTION	PRICE/DELIVERY
EM-ALFA	PLUTONE LINE BELL VACUUM PACKAGING MACHINE, Mod.ALFA, with mm. CHAMBER. 260x300x120h, 250 mm SEALING BAR, DIGITAL CONTROLS, V. 230/1 - Kw 0.75 - external dimensions mm. 320x500x270h	€ 877,74 <i>VAT excluded</i> Shipping to be calculated Delivery from 4 to 9 days

PROFESSIONAL DESCRIPTION

PLUTONE LINE BENCH VACUUM PACKAGING MACHINE, Mod.ALFA, CE standards:

- **VACUUM CHAMBER 260x300x120h mm**, made of **stainless steel** molded in a single piece with rounded corners for maximum hygiene and ease of cleaning;
- **250 mm WELDING BAR**, with completely removable wiring;
- **Single-program DIGITAL CONTROL** panel with manually activated **timed vacuum percentage**,
- **8 metres/cubic/hour VACUUM PUMP** ;
- **Standard filling platforms** ;
- Transparent tank lid with **automatic piston lifting at the end of the work cycle** ;
- **1 work program that can be modified and stored** thanks to a practical and intuitive control panel;
- **Pump self-cleaning system** for removing water and humidity;
- Optimal times and reduced maintenance costs;
- **GASTROVAC function** for creating **external vacuum** in GN containers;
- **EXTRAVAC function** which offers a **second vacuum phase of 5 seconds** (suitable for minced and boned meat);
- **Emergency button** for blocking the appliance + rapid welding;
- Carter with 90° opening to facilitate access to the inside of the packaging machine;
- Adjustable zips;
-
- **Note** : Possibility of external vacuum with the use of embossed envelopes, (as visible in the photo);
-

OPTIONS/ACCESSORIES



- **Inclined surface for packaging liquid products** (Code EM-PI)
- Cart for machine support (EM-CR)
- **Possibility of vacuuming in external containers** or gastro-norm containers using a specific kit (Code EM-TUBOGN)

CE MARK
MADE IN ITALY

TECHNICAL CARD

power supply	Monofase
Volts	V 230/1
frequency (Hz)	50
motor power capacity (Kw)	0,75
net weight (Kg)	32
gross weight (Kg)	42
breadth (mm)	320
depth (mm)	500
height (mm)	270

TECHNICAL CARD

CODE/PICTURES	DESCRIPTION	PRICE/DELIVERY
EM-PI 	Inclined plane, Mod.PI Inclined surface for liquid packaging, suitable for bell-shaped packaging machines	€ 85,74 <i>VAT excluded</i> Shipping to be calculated Delivery from 4 to 9 days
EM-TUBOGN 	Tube with adapter sleeve in gastro containers Tube with adapter sleeve in gastro containers	€ 102,01 <i>VAT excluded</i> Shipping to be calculated Delivery

EM-CR



Machine Support Trolley, Mod. CR
Support trolley

€ 282,20

VAT excluded
Shipping to be calculated

Delivery from 4 to 9 days



STANDARD FUNCTIONS PER CONFEZIONATRICI A CAMPANA


STANDARD FUNCTION ONLY FOR CHAMBER MACHINES



Pannello digitale
Digital panel



Sistema autopulizia olio
Oil made auto cleaning system



Pannello comandi a totale tenuta
contro umidità
Waterproof control Panel



Carter apribile a 90°
90° openable carter



Barre saldanti estraibili
Removable sealing bars



Vasca inox con angoli stondati
senza saldature
Entirely printed stainless steel
vacuum chamber, with internal
round corners



Connessione per attacco gastrovac
Connection for the gastrovac system



Set tavole di riempimento in
polietilene
Polyethylene filling squares set



OPTIONAL PER CONFEZIONATRICI A CAMPANA

OPTIONALS ONLY FOR CHAMBER MACHINES



Pompa Busch
Busch Pump



Carrrello supporto macchina
Charriot on wheels



Piano inclinato per liquidi
Inclined plane for liquids



Tensione e frequenza speciale
Voltage and speciale frequency

Modifica parametri vuoto / saldatura
used to modify vacuum/sealing

Funzione Gas Inerte
Attivata (LED ACCESSO)
Inert gas function on
(LED on)

1. Settaggio % di vuoto
2. Settaggio tempo di saldatura
3. Attivazione funzione saldatura rapida
4. Attivazione funzione VAC STOP:
interruzione anticipata del ciclo di vuoto

1. Setting of the vacuum percentage
2. Setting of the sealing time
3. Activation of RAPID SEALING. If you push the button once
4. Activation of VAC STOP FUNCTION (stop in advance the vacuum cycle) if you push the button twice



Accensione / Spegnimento
confezionatrice
switch on / switch off of the
vacuum packaging machine

Funzione di vuoto in
continuo, per aspirazione
in contenitori gastro
nonstop vacuum function: done
with suction in gastro bowls

Definizione della percentuale
di vuoto raggiunta in camera
vacuum level reached in the
chamber

Funzione di pulizia olio pompa
del vuoto.
Premendo il tasto per tre secon-
di a campana chiusa
pushing the button for three
seconds (only when the bell is
closed) the cleaning function of
the vacuum pump begins

Definizione tempo di saldatura
(espresso in secondi)
sealing time (in seconds)